



SPA312

**SPD T1+T2+T3 3P 12.5kA with remote contact TN-C**

**Technical Features**

**Electric current**

Max. discharge (I <sub>max</sub> ) L-N(PEN)/ N-PE	75 kA
---	-------

**Network configuration**

Network type	TN-C
--------------	------

**Electric current**

Leakage-current free	Yes
Max. overcurrent protection device, parallel connection (fuse)	160 A

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Electric current**

Lightning impulse current I <sub>imp</sub> (10/350 μs) IEC 61643 L-N(PEN)/ N-PE	12.5 kA 37.5 kA
---	--------------------

**Equipment**

With remote signalling contact	Yes
--------------------------------	-----

**Capacity**

Number of modules	4
-------------------	---

**Voltage**

Voltage protection level U <sub>p</sub> according to IEC 61643-1	1.50 kV
Continuous operating voltage U <sub>c</sub> according to IEC 61643-1	264 V
Rated operational voltage U <sub>e</sub>	240 - 415 V
Voltage level U <sub>p</sub> L-N/PEN IEC 61643-11	1.5 kV

**Architecture**

Number of poles	3
-----------------	---

**Use conditions**

Operating temperature	-40 - 80 °C
-----------------------	-------------

**Dimensions**

Height	99 mm
Width	72 mm
Depth	76.20 mm

**Controls and indicators**

With indicator lamp	Yes
---------------------	-----

**Standards**

Requirement class IEC 61643	T1 T2 T3
-----------------------------	----------------

**Installation, mounting**

Nominal tightening torque	3 - 4.5 Nm
Mounting on	DIN rail

**Connection**

Cross-section of input and output with screws, for flexible conductors	2.5 - 25.0 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	2.5 - 35.0 mm <sup>2</sup>
Cross-section signal contact	0.2 - 25.0 mm <sup>2</sup>

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

---

**Configuration**

With integrated protection fuse	No
---------------------------------	----

---

**Sustainability**

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----