



SPN040R

### Cartridge 40kA 275V for pluggable SPD with reserve

#### Technical Features

##### Capacity

Number of modules

1

##### Voltage

Rated operational voltage Ue

230 - 230 V

Continuous operating voltage Uc according to IEC 61643-1

275 V

Voltage protection level Up according to IEC 61643-1

1.20 kV

##### Electric current

Nominal discharge current In 8 - 20  $\mu$ s L-N(PEN)/N-PE IEC 61643

15 kA

Max. discharge (Imax) L-N(PEN)/ N-PE

40 kA

##### Dimensions

Height

45 mm

Width

18 mm

Depth

45 mm

##### Use conditions

Operating temperature

-40 - 55 °C

##### Network configuration

Network type

TN

TT

##### Standards

Requirement class IEC 61643

T2

##### Frequency

Frequency

50 - 60 Hz

##### Sustainability

Halogen free

Yes

REACH-SVHC free

Yes

RoHS conform

Yes