



SPA412A

SPD 4P monobloc 12.5kA class 1 with light indicator TT

Technical Features

Capacity	
Number of modules	8
Voltage	
Rated operational voltage Ue	230 - 230 V
Continuous operating voltage Uc according to IEC 61643-1	255 V
Voltage protection level Up according to IEC 61643-1	2.50 kV
Electric current	
Nominal discharge current In 8 - 20 μs L-N(PEN)/N-PE IEC 61643	12.5 kA
Max. overcurrent protection device, parallel connection (fuse)	315 A
Max. discharge (Imax) L-N(PEN)/ N-PE	50 kA
Dimensions	
Height	90 mm
Width	144 mm
Depth	68 mm
Use conditions	
Operating temperature	-40 - 60 °C
Network configuration	
Network type	TT TN
Equipment	
With remote signalling contact	No
Standards	
Requirement class IEC 61643	T1
Frequency	
Frequency	50 - 60 Hz
Installation, mounting	
Nominal tightening torque	3.60 - 3.60 Nm
Sustainability	
Halogen free	Yes
RoHS conform	Yes