



TXA208C

8-fold output module 16A/230V~ with manual override without bus supply

**Technical Features**

**Settings**

Supported configuration mode	ETS easy
------------------------------	-------------

**Connectivity**

With bus system KNX	Yes
With bus system KNX radio	No

**Dimensions**

Number of width units	6
-----------------------	---

**Electric current**

Rated current	16 A
---------------	------

**Equipment**

Radio frequency bidirectional	No
With switch for manual switch	Yes

**Power**

Output power	1200 W
--------------	--------

**Voltage**

Rated operational voltage U <sub>e</sub>	230 - 230 V
Operating voltage over bus	21 - 32 V

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Use conditions**

Operating temperature	0 - 45 °C
-----------------------	-----------

**Connection**

Cross-section rigid conductor	0.75 - 2.5 mm <sup>2</sup>
Cross-section flexible conductor	0.75 - 2.5 mm <sup>2</sup>