



TXA228

Output device for 8 shutters or blinds 230V~

Technical Features

Settings

Supported configuration mode

ETS
easy

Installation, mounting

Mounting on

DIN rail

Equipment

With switch for manual switch

Yes

Electric current

Rated current

6 A

Max. switching current

6 A

Use conditions

Operating temperature

0 - 45 °C

Connection

Cross-section flexible conductor

0.75 - 2.5 mm²

Cross-section rigid conductor

0.75 - 2.5 mm²

Capacity

Number of modules

6