



TXA226

Output device for 4 shutters / blinds 24V DC

Technical Features

Settings

Supported configuration mode	ETS easy
------------------------------	-------------

Installation, mounting

Mounting on	DIN rail
-------------	----------

Equipment

With switch for manual switch	Yes
-------------------------------	-----

Electric current

Rated current	6 A
Max. switching current	6 A

Use conditions

Operating temperature	0 - 45 °C
-----------------------	-----------

Connection

Cross-section flexible conductor	0.75 - 2.5 mm ²
Cross-section rigid conductor	0.75 - 2.5 mm ²

Capacity

Number of modules	4
-------------------	---