



4554

Technical Features

Frequency

Transmission bandwidth	100 - 100 MHz
------------------------	---------------

Equipment

Number of outputs	1
-------------------	---

Use conditions

Operating temperature	-40 - 70 °C
-----------------------	-------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Voltage

Rated voltage	72 V
---------------	------

Electric current

Rated current	0.50 A
---------------	--------

Dimensions

Built-in depth	31 mm
----------------	-------

Texts

Outlet	With 45° oblique outlet
--------	-------------------------

Voltage	Suitable for PoE+
---------	-------------------

Installation mode	For screw fastening Without spreader claws
-------------------	---

Protection	None
------------	------

Supporting plate/supporting ring	External eyelets on the supporting ring can be broken off for round designs
----------------------------------	---

Type of connection	With LSA + terminals
--------------------	----------------------