Product Datasheet
75663690



75663690

IP20

B.IQ IR Push Button with Thermostat, 3-Gang, Glass Polar White

Technical Features

Installation, mounting

Mounting on	Flush mounting

Use conditions

Operating temperature	-5 - 45 °C

Functions

With room temperature controller	Yes

Dimensions

Height	128.60 mm
Width	88.50 mm
Depth	16.65 mm

Equipment

Number of actuation points	8

Controls and indicators

With LED indication	Yes

Materials

RAL code	9010
Material	Glass
Surface finish	Glossy

Accessories

Has labelling field	No

Screen

With display	Yes

Texts

Function	For switch, push-button, dimmer, blind and thermostat functions With valve protection function Button help function can be activated
Operating mode	Controller operating modes: comfort, standby, night and frost/heat protection mode
Protection	With dismantling protection
Temperature	Temperature measurement via internal Temperature sensor and/or external communication object (weighting ratio parameterisable) Provision of the internal temperature value via communication object

Scope of delivery

Bus connection included	No