



19660215

**Push-button Black Diamond, TS Crystal, stainless steel matt**

**Technical Features**

**Electric current**

Momentary contact current	1.50 A
---------------------------	--------

**Voltage**

Rated voltage	24 V
---------------	------

**Architecture**

Control/operation element	Push button
Number of poles	1

**Materials**

Surface finish	Matt
Material	Brass Stainless steel
Treatment	Untreated
Transparent	No

**Dimensions**

Height	23 mm
Width	23 mm
Depth	23 mm
Built-in depth	13 mm

**Controls and indicators**

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Accessories**

Has labelling field	No
---------------------	----

**Use conditions**

Operating temperature	-20 - 60 °C
-----------------------	-------------

**Texts**

Imprint	Without imprint
Installation mode	For screw fastening
Switch mode	Normally open contact
Type of connection	With plug-in terminals