



19650203

Push-button Topaz, TS Crystal, gold glossy

Technical Features

Electric current

Momentary contact current	1.50 A
---------------------------	--------

Voltage

Rated voltage	24 V
---------------	------

Architecture

Control/operation element	Push button
Number of poles	1

Materials

Surface finish	Glossy
Material	Brass
Treatment	Untreated
Transparent	No

Dimensions

Height	23 mm
Width	23 mm
Depth	23 mm
Built-in depth	13 mm

Controls and indicators

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Accessories

Has labelling field	No
---------------------	----

Use conditions

Operating temperature	-20 - 60 °C
-----------------------	-------------

Texts

Imprint	Without imprint
Installation mode	For screw fastening
Switch mode	Normally open contact
Type of connection	With plug-in terminals