



19650208

**Push-button Siam, TS Crystal, gold glossy**

**Technical Features**

**Electric current**

Momentary contact current 1.50 A

**Voltage**

Rated voltage 24 V

**Architecture**

Control/operation element Push button

Number of poles 1

**Materials**

Surface finish Glossy

Material Brass

Treatment Untreated

Transparent No

**Dimensions**

Height 23 mm

Width 23 mm

Depth 23 mm

Built-in depth 13 mm

**Controls and indicators**

Number of buttons 1

Type of push button Single push button

With feedback signal contact No

**Safety**

Ingress Protection (IP) class IP20

**Accessories**

Has labelling field No

**Use conditions**

Operating temperature -20 - 60 °C

**Texts**

Imprint Without imprint

Installation mode For screw fastening

Switch mode Normally open contact

Type of connection With plug-in terminals