



19650208

Push-button Siam, TS Crystal, gold glossy

Technical Features

Electric current

Momentary contact current	1.50 A
---------------------------	--------

Voltage

Rated voltage	24 V
---------------	------

Architecture

Control/operation element	Push button
---------------------------	-------------

Number of poles	1
-----------------	---

Materials

Surface finish	Glossy
----------------	--------

Material	Brass
----------	-------

Treatment	Untreated
-----------	-----------

Transparent	No
-------------	----

Dimensions

Height	23 mm
--------	-------

Width	23 mm
-------	-------

Depth	23 mm
-------	-------

Built-in depth	13 mm
----------------	-------

Controls and indicators

Number of buttons	1
-------------------	---

Type of push button	Single push button
---------------------	--------------------

With feedback signal contact	No
------------------------------	----

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Accessories

Has labelling field	No
---------------------	----

Use conditions

Operating temperature	-20 - 60 °C
-----------------------	-------------

Texts

Imprint	Without imprint
---------	-----------------

Installation mode	For screw fastening
-------------------	---------------------

Switch mode	Normally open contact
-------------	-----------------------

Type of connection	With plug-in terminals
--------------------	------------------------