Product Datasheet
75665699



75665699




B.IQ IR Push Button with Thermostat, 5-Gang, Matt Polar White

Technical Features

Installation, mounting

Mounting on	Flush mounting

Use conditions

Operating temperature	-5 - 45 °C

Functions

With room temperature controller	Yes

Dimensions

Height	187.80 mm
Width	88.50 mm
Depth	15 mm

Equipment

Number of actuation points	12

Controls and indicators

With LED indication	Yes

Materials

RAL code	9010
Material	Thermoplastic
Surface finish	Matt

Accessories

Has labelling field	Yes

Screen

With display	Yes

Texts

Function	For switch, push-button, dimmer, blind and thermostat functions With valve protection function Button help function can be activated
Operating mode	Controller operating modes: comfort, standby, night and frost/heat protection mode
Protection	With dismantling protection
Temperature	Temperature measurement via internal Temperature sensor and/or external communication object (weighting ratio parameterisable) Provision of the internal temperature value via communication object

Scope of delivery

Bus connection included	No