



JPE243624S25DW1

**Technical Features**

**Connection**

Number of accessible phases	84
-----------------------------	----

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Electric current**

Rated current	250 A
Breaking and opening capacity Idm	0 kA

**Equipment**

With lock	Yes
Has mounting plate	No
Equipped with switch	No switch
Number of switches	0
Type of busbar chassis	Split chassis

**Capacity**

Number of modules	42
-------------------	----

**Weight**

Weight	73 kg
--------	-------

**Dimensions**

Height	1600 mm
Width	600 mm
Depth	250 mm

**Cover, door**

Door/cover is transparent	No
---------------------------	----

**Materials**

Material	Steel
RAL code	7035
Colour	Light grey

**Safety**

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP66
Locking type	3-point lever Key lock

**Architecture**

Number of poles	84
-----------------	----