



TRE501



**Motion detector radio, with battery, IP55, anthracite**

**Technical Features**

**Dimensions**

Installation height	4 - 4 m
---------------------	---------

**Settings**

Supported configuration mode	ETS easy
Minimal duty cycle	5 s

**Functions**

Maximal duty cycle	30 min
--------------------	--------

**Connectivity**

With bus system KNX radio	Yes
---------------------------	-----

**Lighting**

Response brightness adjustable	5 - 1000 lx
--------------------------------	-------------

**Detection**

Detection angle adjustable	45 - 90 °
Detection angle horizontal	220 - 220

**Use conditions**

Operating temperature	-5 - 45 °C
-----------------------	------------

**Materials**

Material	Acrylonitrile-Butadiene-Styrene (ABS) Polycarbonate (PC)
----------	---

**Texts**

Function	Switch-off pre-warning on dimmer inserts With memory function for presence simulation Teach function for response brightness via button With keylock Party function for switching on for 2 hours Reset function (to factory setting)
----------	---