



WXT505



Movement detector 180°, KNX, module, 2,20m

Technical Features

Dimensions

| | |
|---------------------------------|---------------|
| Recommended installation height | 2.20 - 2.20 m |
|---------------------------------|---------------|

Settings

| | |
|------------------------------|-------------|
| Supported configuration mode | ETS easy |
| Minimal duty cycle | 10 s |

Functions

| | |
|--------------------|--------|
| Maximal duty cycle | 30 min |
|--------------------|--------|

Connectivity

| | |
|---------------------------|----|
| With bus system KNX radio | No |
|---------------------------|----|

Voltage

| | |
|----------------------------|-----------|
| Operating voltage over bus | 21 - 32 V |
|----------------------------|-----------|

Scope of delivery

| | |
|-------------------------|-----|
| Bus connection included | Yes |
|-------------------------|-----|

Electric current

| | |
|---------------------------------------|-------|
| Bus current consumption data transfer | 10 mA |
|---------------------------------------|-------|

Lighting

| | |
|--------------------------------|-------------|
| Response brightness adjustable | 5 - 1000 lx |
|--------------------------------|-------------|

Detection

| | |
|----------------------------|-----------|
| Detection angle adjustable | 45 - 90 ° |
| Detection angle horizontal | 90 - 180 |

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5 - 45 °C |
|-----------------------|------------|

Materials

| | |
|----------|---------------|
| Material | Thermoplastic |
|----------|---------------|

Texts

| | |
|-------------------|--------------------------------------------------------------|
| Push button | With button for automatic/permanent ON/permanent OFF |
| Operating mode | With 3 operating modes: automatic/permanent ON/permanent OFF |
| Function | Presence simulation With party function |
| Installation mode | With spreader claws With dismantling protection |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|