



WXF063

**Touch dimmer Gallery**

**Technical Features**

**Voltage**

Operating voltage	230 - 230 V
-------------------	-------------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Materials**

Colour	Grey
RAL code	7011
Material	Polycarbonate (PC)

**Dimensions**

Height	45 mm
Width	45 mm

**Architecture**

Control/operation element	Single push button
---------------------------	--------------------

**Lighting**

LED lamp power	70 W
----------------	------

**Use conditions**

Operating temperature	-10 - 35 °C
-----------------------	-------------

**Capacity**

Number of modules	2
-------------------	---

**Texts**

Dimming principle	Phase cut-on or cut-off according to load type, self-learning
Installation mode	For catch fixing
Type of connection	With screw terminals
Operation and control	No Bluetooth interface

**Sustainability**

RoHS conform	Yes
--------------	-----