



3315391909



## USB socket outlet

### Technical Features

#### Connection

Connector/plug type	USB
Number of connections	2

#### Frequency

Audio frequency	20 - 20 Hz
-----------------	------------

#### Materials

Colour	Polar white
RAL code	9010
Surface finish	Matt
Material	Metal Plastic
Treatment	Untreated

#### Dimensions

Height	71 mm
Width	71 mm
Depth	36.40 mm
Built-in depth flush-mounted boxes	27 mm
Built-in depth	24.90 mm

#### Connectivity

Mounting type	Screw mounting
---------------	----------------

#### Equipment

Shielded	Yes
With dust cover	No

#### Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK05

#### Texts

Outlet	With straight outlet
Labelling	Without labelling field
Supporting plate/supporting ring	With supporting ring

#### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes