



3315391909



**USB socket outlet**

**Technical Features**

**Connection**

Connector/plug type	USB
Number of connections	2

**Frequency**

Audio frequency	20 - 20 Hz
-----------------	------------

**Materials**

Colour	Polar white
RAL code	9010
Surface finish	Matt
Material	Metal Plastic
Treatment	Untreated

**Dimensions**

Height	71 mm
Width	71 mm
Depth	36.40 mm
Built-in depth flush-mounted boxes	27 mm
Built-in depth	24.90 mm

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Equipment**

Shielded	Yes
With dust cover	No

**Safety**

Ingress Protection (IP) class	IP20
Impact resistance IK	IK05

**Texts**

Outlet	With straight outlet
Labelling	Without labelling field
Supporting plate/supporting ring	With supporting ring

**Suitable for**

S.x/B.x	
---------	--

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes