



MM509N

Motor protection circuit breaker 3P 4-6.3A ; 1.1/2.2 kW at 230/415V

Technical Features

Electric current	
Rated current	6.30 A

Dimensions	
Height	140 mm
Width	45 mm
Depth	75 mm

Architecture	
Control/operation element	Short rotary handle
Number of poles	3

Voltage	
Rated impulse withstand voltage Uimp	6000 V
Overvoltage category according to IEC 60947-1	3
Type voltage supply	AC

Connectivity	
Connection type control and aux contact	Screw terminal

Equipment	
Sealable	No
With auxiliary contact	No
With thermal protection	Yes

Safety	
Ingress Protection (IP) class	IP20

Installation, mounting	
Mounting on	DIN rail

Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

