



MM502N

Motor protection circuit breaker 3P 0.16-0.25A ; 0.03/0.06 kW at 230/415V 230/41

**Technical Features**

**Electric current**

Rated current	0.25 A
---------------	--------

**Dimensions**

Height	140 mm
Width	45 mm
Depth	75 mm

**Architecture**

Control/operation element	Short rotary handle
Number of poles	3

**Voltage**

Rated impulse withstand voltage Uimp	6000 V
Overtoltage category according to IEC 60947-1	3
Type voltage supply	AC

**Connectivity**

Connection type control and aux contact	Screw terminal
---	----------------

**Equipment**

Sealable	No
With auxiliary contact	No
With thermal protection	Yes

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Installation, mounting**

Mounting on	DIN rail
-------------	----------

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes

**Illustrations | Drawings**

