



MM502N

Motor protection circuit breaker 3P 0.16-0.25A ; 0.03/0.06 kW at 230/415V 230/41

Technical Features

Electric current

| | |
|---------------|--------|
| Rated current | 0.25 A |
|---------------|--------|

Dimensions

| | |
|--------|--------|
| Height | 140 mm |
| Width | 45 mm |
| Depth | 75 mm |

Architecture

| | |
|---------------------------|---------------------|
| Control/operation element | Short rotary handle |
| Number of poles | 3 |

Voltage

| | |
|---|--------|
| Rated impulse withstand voltage Uimp | 6000 V |
| Overvoltage category according to IEC 60947-1 | 3 |
| Type voltage supply | AC |

Connectivity

| | |
|---|----------------|
| Connection type control and aux contact | Screw terminal |
|---|----------------|

Equipment

| | |
|-------------------------|-----|
| Sealable | No |
| With auxiliary contact | No |
| With thermal protection | Yes |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Installation, mounting

| | |
|-------------|----------|
| Mounting on | DIN rail |
|-------------|----------|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |

Illustrations | Drawings

