



WNC044

Cubyko LT double push button NO/NF wall mounted grey IP55

Technical Features

Electric current

Momentary contact current	10 A
---------------------------	------

Voltage

Rated voltage	250 V
---------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Architecture

Control/operation element	Double push button
Number of poles	2

Materials

Colour	Grey
Surface finish	Satin finish
Material	Thermoplastic
Treatment	Untreated
Transparent	No
Backside internal	Mat

Dimensions

Height	55.90 mm
Width	55.90 mm
Depth	32.30 mm
Built-in depth flush-mounted boxes	0 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Controls and indicators

Indicator lamp	As an accessory
Number of buttons	2
Type of push button	Series push button
With feedback signal contact	No

Connectivity

Type of connection	quickconnect
--------------------	--------------

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK05

Accessories

Has labelling field	No
---------------------	----

Use conditions

Operating temperature	-25 - 35 °C
-----------------------	-------------

Texts

Imprint	Without imprint
Installation mode	For screw fastening
Sealing	With full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside
Terminal	With Wago clip-in 2-wire connection terminal for wiring With two clip-in places for Wago 2-wire connection terminals in the housing floor
Type of connection	With plug-in terminals

Suitable for

Hager cubyko

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes