



WNE023

**Cubyko LT push-button 1F with control light flush mounted grey IP55**

**Technical Features**

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Architecture**

Control/operation element	Single push button
---------------------------	--------------------

**Materials**

Colour	Grey
Surface finish	Satin finish
Material	Polypropylene (PP)
Backside internal	Matt

**Dimensions**

Height	75 mm
Width	75 mm
Depth	40 mm
Built-in depth flush-mounted boxes	40 mm

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Controls and indicators**

Type of push button	Single push button
---------------------	--------------------

**Connectivity**

Type of connection	quickconnect
--------------------	--------------

**Safety**

Ingress Protection (IP) class	IP20
Impact resistance IK	IK07

**Accessories**

Has labelling field	No
---------------------	----

**Use conditions**

Operating temperature	-15 - 30 °C
-----------------------	-------------

**Suitable for**

cubyko	
--------	--

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes