



WRDS2BS

2 Gang Dimmer Switch 250W Brushed Steel

Technical Features

Voltage

Operating voltage 240 - 240 V

Frequency

Frequency 50 - 60 Hz

Materials

Material Stainless steel

Dimensions

Height 86 mm

Width 86 mm

Depth 31 mm

Architecture

Control/operation element Push & rotative switch

Texts

Dimming principle Phase cut-on

Type of connection With screw terminals

Operation and control No Bluetooth interface

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes