



WNA022

## Cubyko LT push-button 10/1F composable grey IP55

### Technical Features

#### Electric current

Momentary contact current	10 A
---------------------------	------

#### Voltage

Rated voltage	250 V
---------------	-------

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Architecture

Control/operation element	Rocker
---------------------------	--------

#### Materials

Colour	Grey
Surface finish	Satin finish
Material	Thermoplastic
Treatment	Untreated
Transparent	No

#### Dimensions

Height	71 mm
Width	71 mm
Depth	43 mm
Built-in depth flush-mounted boxes	40 mm

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Controls and indicators

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

#### Connectivity

Type of connection	quickconnect
--------------------	--------------

#### Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK05

#### Accessories

Has labelling field	No
---------------------	----

#### Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

#### Texts

Imprint	Without imprint
Installation mode	For screw fastening
Type of connection	With plug-in terminals

#### Suitable for

Hager cubyko	
--------------	--

#### Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes