



WNA045B

### Cubyko LT 2-gang 2-way push-button 10/1F composable with light white IP55

#### Technical Features

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

##### Architecture

|                           |                    |
|---------------------------|--------------------|
| Control/operation element | Double push button |
|---------------------------|--------------------|

##### Materials

|                |               |
|----------------|---------------|
| Colour         | Pure white    |
| Surface finish | Satin finish  |
| Material       | Thermoplastic |

##### Dimensions

|                                    |       |
|------------------------------------|-------|
| Height                             | 75 mm |
| Width                              | 75 mm |
| Depth                              | 40 mm |
| Built-in depth flush-mounted boxes | 40 mm |

##### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

##### Controls and indicators

|                              |                    |
|------------------------------|--------------------|
| Number of buttons            | 2                  |
| Type of push button          | Single push button |
| With feedback signal contact | No                 |

##### Connectivity

|                    |              |
|--------------------|--------------|
| Type of connection | quickconnect |
|--------------------|--------------|

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
| Impact resistance IK          | IK07 |

##### Accessories

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

##### Use conditions

|                       |             |
|-----------------------|-------------|
| Operating temperature | -15 - 30 °C |
|-----------------------|-------------|

##### Texts

|                   |                     |
|-------------------|---------------------|
| Installation mode | For screw fastening |
|-------------------|---------------------|

##### Suitable for

|              |  |
|--------------|--|
| Hager cubyko |  |
|--------------|--|

##### Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |