



WNA023B

Cubyko LT push-button 1F with control light composable white IP55

Technical Features

Frequency

Frequency	50 - 60 Hz
-----------	------------

Architecture

Control/operation element	Single push button
---------------------------	--------------------

Materials

Colour	Pure white
Surface finish	Satin finish
Material	Polypropylene (PP)

Dimensions

Height	75 mm
Width	75 mm
Depth	40 mm
Built-in depth flush-mounted boxes	40 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Controls and indicators

Number of buttons	1
Type of push button	Single push button

Connectivity

Type of connection	quickconnect
--------------------	--------------

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK07

Accessories

Has labelling field	No
---------------------	----

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Suitable for

Hager cubyko	
--------------	--

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes