



WRDP84NIPSW

20A Double Pole Switch Isolation Function with LED Polished Steel White Insert

Technical Features

Installation, mounting

Mounting on Flush mounting

Materials

Surface finish Glossy
Matt
Material Stainless steel
Treatment Untreated

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 86 x 86 mm
Built-in depth 21.90 mm
Built-in depth flush-mounted boxes 25 mm

Safety

Ingress Protection (IP) class IP20

Architecture

Control/operation element Single rocker

Electric current

Rated current 20 A

Texts

Lighting With control LED for ON
Switch mode 2-pole