



WMDP84NI

20A Double Pole Switch Isolation Function & LED Indicator

Technical Features

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Materials

| | |
|----------------|-------------------|
| Surface finish | Glossy Matt |
| Material | Urea formaldehyde |
| Treatment | Untreated |

Identification

| | |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

Connectivity

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Controls and indicators

| | |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

Dimensions

| | |
|------------------------------------|------------|
| Dimensions | 86 x 86 mm |
| Built-in depth | 21.90 mm |
| Built-in depth flush-mounted boxes | 25 mm |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Architecture

| | |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

Electric current

| | |
|---------------|------|
| Rated current | 20 A |
|---------------|------|

Texts

| | |
|-------------|-------------------------|
| Lighting | With control LED for ON |
| Switch mode | 2-pole |