



WRDS4BS

#### 4 Gang Dimmer Switch 250W Brushed Steel

##### Technical Features

###### Voltage

Operating voltage	240 - 240 V
-------------------	-------------

###### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Materials

Material	Stainless steel
----------	-----------------

##### Dimensions

Height	86 mm
Width	146 mm
Depth	31 mm

##### Architecture

Control/operation element	Push & rotative switch
---------------------------	------------------------

##### Texts

Dimming principle	Phase cut-on
Type of connection	With screw terminals
Operation and control	No Bluetooth interface

##### Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes