



WRSS82PSB-USBAC

**DP Switched Socket 13A 2G USB A+C ports Polished Steel Black Raised**

**Technical Features**

**Electric current**

Rated current 13 A

**Frequency**

Frequency 50 - 50 Hz

**Materials**

Surface finish Glossy

Material Stainless steel

**Dimensions**

Height 86 mm

Width 146 mm

Depth 18 mm

Built-in depth flush-mounted boxes 25 mm

**Installation, mounting**

Mounting on Flush mounting

Mounting-/Connection Position Horizontal

**Connectivity**

Type of connection Screw terminal

Mounting type Screw mounting

Connector/plug type USB AC

**Equipment**

Connector/plug type socket outlet British Standard

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

**Accessories**

Has labelling field No

**Capacity**

Number of modules 0

**Safety**

Ingress Protection (IP) class IP20

**Functions**

With orientation lighting No

With function lighting No

**Texts**

Imprint With imprint

Cover Full cover plate

Wiring With double earth connection

Protection Enhanced contact protection

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes