




WMS812LN

### 13A Double Pole Key Switch Socket with LED Indicator

#### Technical Features

##### Electric current

|               |      |
|---------------|------|
| Rated current | 13 A |
|---------------|------|

##### Materials

|                |                                    |
|----------------|------------------------------------|
| Surface finish | Glossy                             |
| Material       | Thermoplastic<br>Urea formaldehyde |
| Treatment      | Untreated                          |

##### Dimensions

|                                    |       |
|------------------------------------|-------|
| Height                             | 86 mm |
| Width                              | 86 mm |
| Depth                              | 26 mm |
| Built-in depth flush-mounted boxes | 25 mm |

##### Installation, mounting

|                               |                |
|-------------------------------|----------------|
| Mounting on                   | Flush mounting |
| Mounting-/Connection Position | Horizontal     |

##### Connectivity

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
| Mounting type      | Screw mounting |

##### Equipment

|                                   |                  |
|-----------------------------------|------------------|
| Connector/plug type socket outlet | British Standard |
| Rotated central insert            | No               |
| With hinged lid                   | No               |
| With round protective earth pin   | No               |
| With signal lamp                  | No               |

##### Accessories

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

##### Capacity

|                   |   |
|-------------------|---|
| Number of modules | 0 |
|-------------------|---|

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

##### Functions

|                           |    |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting    | No |

##### Texts

|            |                             |
|------------|-----------------------------|
| Imprint    | Without imprint             |
| Cover      | Full cover plate            |
| Wiring     | With earth connection       |
| Protection | Enhanced contact protection |

##### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|