



WNA301

### Cubyko LT shutter push-button with stop symbol composable grey IP55

#### Technical Features

##### Electric current

Momentary contact current	10 A
---------------------------	------

##### Voltage

Rated voltage	250 V
---------------	-------

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Architecture

Control/operation element	Double rocker
---------------------------	---------------

##### Materials

Colour	Grey
Surface finish	Satin finish
Material	Thermoplastic
Treatment	Untreated
Transparent	No

##### Dimensions

Height	75 mm
Width	75 mm
Depth	32 mm
Built-in depth flush-mounted boxes	40 mm

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Controls and indicators

Number of buttons	2
Type of push button	Single push button
With feedback signal contact	No

##### Connectivity

Type of connection	quickconnect
--------------------	--------------

##### Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK05

##### Accessories

Has labelling field	No
---------------------	----

##### Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

##### Texts

Imprint	With imprinted symbol arrow
Installation mode	For screw fastening
Switch mode	With mechanical and electrical interlock to prevent mutual activation
Type of connection	With plug-in terminals

##### Suitable for

Hager cubyko	
--------------	--

##### Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes