



WNA301



Cubyko LT shutter push-button with stop symbol composable grey IP55

Technical Features

Electric current

Momentary contact current 10 A

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Architecture

Control/operation element Double rocker

Materials

Colour Grey
 Surface finish Satin finish
 Material Thermoplastic
 Treatment Untreated
 Transparent No

Dimensions

Height 75 mm
 Width 75 mm
 Depth 32 mm
 Built-in depth flush-mounted boxes 40 mm

Installation, mounting

Mounting on Flush mounting

Controls and indicators

Number of buttons 2
 Type of push button Single push button
 With feedback signal contact No

Connectivity

Type of connection quickconnect

Connection

Connector/plug type Turn screw lock

Safety

Ingress Protection (IP) class IP20
 Impact resistance IK IK05

Accessories

Has labelling field No

Use conditions

Operating temperature -15 - 30 °C

Texts

Imprint With imprinted symbol arrow
 Installation mode For screw fastening
 Switch mode With mechanical and electrical interlock to prevent mutual activation
 Type of connection With plug-in terminals

Suitable for

cubyko

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes