



WRSS82PSW-USBAC

DP Switched Socket 13A 2G USB A+C ports Polished Steel White Raised

Technical Features

Electric current

Rated current 13 A

Frequency

Frequency 50 - 50 Hz

Materials

Surface finish Glossy

Material Stainless steel

Dimensions

Height 86 mm

Width 146 mm

Depth 18 mm

Built-in depth flush-mounted boxes 25 mm

Installation, mounting

Mounting on Flush mounting

Mounting-/Connection Position Horizontal

Connectivity

Type of connection Screw terminal

Mounting type Screw mounting

Connector/plug type USB AC

Equipment

Connector/plug type socket outlet British Standard

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

Accessories

Has labelling field No

Capacity

Number of modules 0

Safety

Ingress Protection (IP) class IP20

Functions

With orientation lighting No

With function lighting No

Texts

Imprint With imprint

Cover Full cover plate

Wiring With double earth connection

Protection Enhanced contact protection

Sustainability

REACH-SVHC free Yes

RoHS conform Yes