



WNA003B

Cubyko LT 2-way switch with control light composable white IP55

Technical Features

Electric current

Switching current	10 A
-------------------	------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Voltage

Rated voltage	250 V
---------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Polar white
RAL code	9010
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

Identification

Assembly arrangement	Control element
----------------------	-----------------

Connectivity

Mounting type	Screw mounting
---------------	----------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	55 x 55 mm
Built-in depth	12 mm
Built-in depth flush-mounted boxes	40 mm

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK08

Architecture

Control/operation element	Single rocker
---------------------------	---------------

Electric current

Rated current	10 A
---------------	------

Connection

Type of contacts	2-way
Connector/plug type	Turn screw lock

Texts

Installation mode	For screw fastening
Type of connection	With N-terminal With plug-in terminals
Lighting	With red 230 V LED unit For monitoring circuit
Switch mode	Change-over

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes