



WNA003B

IP55

Cubyko LT 2-way switch with control light composable white IP55

Technical Features

Electric current

Switching current 10 A

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Materials

Colour Polar white

RAL code 9010

Surface finish Matt

Material Thermoplastic

Treatment Untreated

Identification

Assembly arrangement Control element

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 55 x 55 mm

Built-in depth 12 mm

Built-in depth flush-mounted boxes 40 mm

Safety

Impact resistance IK IK08

Usable in higher IP class IP55 with closed cover

Electric current

Rated current 10 A

Connection

Type of contacts 2-way

Connector/plug type Turn screw lock

Texts

Installation mode For screw fastening

Type of connection With N-terminal

With plug-in terminals

Lighting With red 230 V LED unit

For monitoring circuit

Push button No

Sustainability

REACH-SVHC free Yes

RoHS conform Yes