



WNA040



Cubyko LT 2-gang 2-way switch composable grey IP55

Technical Features

Electric current

Switching current 10 A

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Materials

Colour Grey
RAL code 7011
Surface finish Matt
Material Thermoplastic
Treatment Untreated

Identification

Assembly arrangement Control element

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 2

Dimensions

Dimensions 70 x 70 mm
Built-in depth 12 mm
Built-in depth flush-mounted boxes 40 mm

Safety

Impact resistance IK IK05
Usable in higher IP class IP55 with closed cover

Electric current

Rated current 10 A

Connection

Type of contacts 2-way
Connector/plug type Turn screw lock

Texts

Installation mode For screw fastening
Type of connection With plug-in terminals
Lighting Without lighting (cannot be illuminated)
Push button No

Sustainability

Halogen free Yes
REACH-SVHC free Yes
RoHS conform Yes