



WMDP84FOI

**20A Double Pole Switch Isolation Function & Flex Outlet**

**Technical Features**

**Installation, mounting**

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

**Voltage**

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

**Materials**

|                |                   |
|----------------|-------------------|
| Surface finish | Glossy<br>Matt    |
| Material       | Urea formaldehyde |
| Treatment      | Untreated         |

**Identification**

|                      |                                     |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

**Connectivity**

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

**Controls and indicators**

|                   |   |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

**Dimensions**

|                                    |            |
|------------------------------------|------------|
| Dimensions                         | 86 x 86 mm |
| Built-in depth                     | 21.90 mm   |
| Built-in depth flush-mounted boxes | 25 mm      |

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Architecture**

|                           |               |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

**Electric current**

|               |      |
|---------------|------|
| Rated current | 20 A |
|---------------|------|

**Texts**

|             |                         |
|-------------|-------------------------|
| Lighting    | With control LED for ON |
| Switch mode | 2-pole                  |

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |