



WNA045

Cubyko LT 2-gang 2-way push-button 10/1F composable with light grey IP55

Technical Features

Frequency

Frequency	50 - 60 Hz
-----------	------------

Architecture

Control/operation element	Double push button
---------------------------	--------------------

Materials

Colour	Grey
Surface finish	Satin finish
Material	Thermoplastic

Dimensions

Height	75 mm
Width	75 mm
Depth	40 mm
Built-in depth flush-mounted boxes	40 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Controls and indicators

Number of buttons	2
Type of push button	Single push button
With feedback signal contact	No

Connectivity

Type of connection	quickconnect
--------------------	--------------

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK07

Accessories

Has labelling field	No
---------------------	----

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Texts

Installation mode	For screw fastening
-------------------	---------------------

Suitable for

Hager cubyko	
--------------	--

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes