



WMDP84FONI

**20A Double Pole Switch Isolation Function & LED Indicator & Flex Outlet**

**Technical Features**

**Installation, mounting**

Mounting on Flush mounting

**Voltage**

Rated voltage 250 V

**Materials**

Surface finish Glossy  
Matt

Material Urea formaldehyde

Treatment Untreated

**Identification**

Assembly arrangement Basic element with full cover plate

**Connectivity**

Mounting type Screw mounting

**Controls and indicators**

Number of buttons 1

**Dimensions**

Dimensions 86 x 86 mm

Built-in depth 21.90 mm

Built-in depth flush-mounted boxes 25 mm

**Electric current**

Rated current 20 A

**Texts**

Lighting With control LED for ON

Push button No

Imprint With clear terminal markings