



WMDP84FONI

20A Double Pole Switch Isolation Function & LED Indicator & Flex Outlet

Technical Features

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Materials

Surface finish Glossy
Matt

Material Urea formaldehyde

Treatment Untreated

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 86 x 86 mm

Built-in depth 21.90 mm

Built-in depth flush-mounted boxes 25 mm

Electric current

Rated current 20 A

Texts

Lighting With control LED for ON

Push button No

Imprint With clear terminal markings