



WRDP84NIBSW

20A Double Pole Switch Isolation Function with LED Brushed Steel White Insert

Technical Features

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Materials

Surface finish	Glossy Matt
----------------	-------------

Material

Material	Stainless steel
----------	-----------------

Treatment

Treatment	Untreated
-----------	-----------

Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

Connectivity

Mounting type	Screw mounting
---------------	----------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	86 x 86 mm
------------	------------

Built-in depth	21.90 mm
----------------	----------

Built-in depth flush-mounted boxes	25 mm
------------------------------------	-------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Architecture

Control/operation element	Single rocker
---------------------------	---------------

Electric current

Rated current	20 A
---------------	------

Texts

Lighting	With control LED for ON
----------	-------------------------

Switch mode	2-pole
-------------	--------