



WNA022B

Cubyko LT push-button 10/1F composable white IP55

Technical Features

Electric current

Momentary contact current	10 A
---------------------------	------

Voltage

Rated voltage	250 V
---------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Architecture

Control/operation element	Rocker
---------------------------	--------

Materials

Colour	Polar white
Surface finish	Satin finish
Material	Thermoplastic
Treatment	Untreated
Transparent	No

Dimensions

Height	71 mm
Width	71 mm
Depth	43 mm
Built-in depth flush-mounted boxes	40 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Controls and indicators

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

Connectivity

Type of connection	quickconnect
--------------------	--------------

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK05

Accessories

Has labelling field	No
---------------------	----

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Texts

Imprint	Without imprint
Installation mode	For screw fastening
Type of connection	With plug-in terminals

Suitable for

Hager cubyko	
--------------	--

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes