



WGMS213SDPAS

## 13A TWIN DP SWITCHED SOCKET,AS

### Technical Features

#### Electric current

Rated current	13 A
Output current	0 mA

#### Voltage

Rated voltage	250 V
Nominal voltage	220-250 V
Output voltage	0-0 V

#### Use conditions

Operating temperature	-20-45 °C
-----------------------	-----------

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Power

Output power	0 W
Power consumption standby	0 W

#### Materials

Colour	Aurora silver
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Coated
Contains recycled material (% of total plastic weight)	0 %

#### Dimensions

Height	18 mm
Width	86 mm
Depth	18 mm
Built-in depth flush-mounted boxes	35 mm
Built-in depth	18 mm

#### Connection

Connector/plug type	British Standard
Cross-section flexible conductor without wire end sleeve	0.08 - 4 mm <sup>2</sup>

#### Installation, mounting

Mounting on	Flush mounting
Mounting-/Connection Position	Back

#### Connectivity

Type of connection	Screw terminal
With claw mounting	No
Mounting type	Screw mounting
Connector/plug type USB	British Standard

#### Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

#### Accessories

Has labelling field	No
Pre-equipped with	None

---

**Capacity**

Number of modules	0
-------------------	---

---

**Safety**

With enhanced contact protection	No
Impact resistance IK	IK02
Ingress Protection (IP) class	IP20

---

**Functions**

With orientation lighting	No
With function lighting	No

---

**Identification**

With imprint	No
--------------	----

---

**Suitable for**

shark	
-------	--

---

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes