



WGMS213S

## 13A TWIN SWITCHED SOCKET

### Technical Features

#### Electric current

Rated current	13 A
Output current	0 mA

#### Voltage

Rated voltage	250 V
Nominal voltage	220-250 V
Output voltage	0-0 V

#### Use conditions

Operating temperature	-20-45 °C
-----------------------	-----------

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Power

Output power	0 W
Power consumption standby	0 W

#### Materials

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated
Contains recycled material (% of total plastic weight)	0 %

#### Dimensions

Height	28 mm
Width	86 mm
Depth	18 mm
Built-in depth flush-mounted boxes	35 mm
Built-in depth	18 mm

#### Connection

Connector/plug type	British Standard
Cross-section flexible conductor without wire end sleeve	0.08 - 4 mm <sup>2</sup>

#### Installation, mounting

Mounting on	Flush mounting
Mounting-/Connection Position	Back

#### Connectivity

Type of connection	Screw terminal
With claw mounting	No
Mounting type	Screw mounting
Connector/plug type USB	British Standard

#### Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

#### Accessories

Has labelling field	No
Pre-equipped with	None

# Product Datasheet

## WGMS213S

---

### Capacity

Number of modules	0
-------------------	---

### Safety

With enhanced contact protection	No
Impact resistance IK	IK02
Ingress Protection (IP) class	IP20

### Functions

With orientation lighting	No
With function lighting	No

### Identification

With imprint	No
--------------	----

### Suitable for

shark

### Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes