
Product Datasheet
WGMS113S



WGMS113S

13A SINGLE SWITCHED SOCKET

Technical Features

Voltage

Rated voltage	250 V

Electric current

Rated current	13 A

Frequency

Frequency	50 - 60 Hz

Materials

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)

Dimensions

Width	86 mm

Equipment

With hinged lid	No

Safety

With enhanced contact protection	No
Ingress Protection (IP) class	IP20

Suitable for

shark

Sustainability

Halogen free	Yes
REACh-SVHC free	Yes
RoHS conform	Yes