



WBHP1R-MB

### Allure Single GPO 10A with round Earth MB

#### Technical Features

##### Electric current

Rated current	10 A
---------------	------

##### Voltage

Nominal voltage	250 - 250 V
-----------------	-------------

##### Frequency

Frequency	50 - 50 Hz
-----------	------------

##### Materials

Colour	Black
--------	-------

##### Installation, mounting

Mounting on	Surface mounting
Mounting-/Connection Position	Horizontal

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No

##### Accessories

Has labelling field	No
---------------------	----

##### Capacity

Number of modules	1
-------------------	---

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Functions

With orientation lighting	No
With function lighting	No

##### Texts

Imprint	Without imprint
Cover	Complete housing

##### Suitable for

allure	
--------	--

##### Sustainability

Halogen free	Yes
RoHS conform	Yes