



4 Module DIN Rail Enclosure

Technical Features

Connection

Number of accessible phases	0
-----------------------------	---

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	100 A
---------------	-------

Equipment

Number of rails	1
Number of rows	1
Number of groups	0
Number of section in width	0
With lock	No
Has neutral terminal block	Yes

Capacity

Number of modules	4
-------------------	---

Functions

Has protection main switch	No
With conduit inlets	No

Scope of delivery

Number of RCCB in enclosure	0
-----------------------------	---

Dimensions

Height	240 mm
Width	149 mm
Depth	102.50 mm

Cover, door

Number of cabinet doors	1
Number of locks	0
Type of handle	Dependent manual operation
Door/cover is transparent	No
Cabinet door type	Single door

Connection

Number of conduit inlets	0
--------------------------	---

Connectivity

Mounting type	Surface mounting
---------------	------------------

Materials

Material	Steel
RAL code	9010
Colour	White

Equipment

Has earthing terminal block	Yes
Has mounting plate	Yes

Materials

Ultraviolet-resistant	No
-----------------------	----

Safety

Protection class	Isolation class I
Impact resistance IK	IK05

Safety

Ingress Protection (IP) class	IP2XC
Locking type	Without lock
Protection class with door	IP4X

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes